


Siren Controls

functions like the AR Timer, and in addition, provides a two-minute hi-lo signal for fire warning.

Both the AR and AF Timers are activated by push buttons on the face of the cabinet.

These timers have contacts with fifteen amperes capacity. Where the load of the control circuit exceeds this amount, an auxiliary line relay may also be necessary. Both timers are available in five-minute versions also—AR5 and AF5.

If desired, AR and AF timers may be activated from remote locations by additional control buttons. Federal Model SO start-only push buttons, connected in parallel, will provide this remote operation. A start/stop-type button is not required since these timers shut off automatically at the end of the three-minute cycle.



Model SS



Model 75

Push Buttons

Push buttons provide remote operation or testing. They can be used with any siren motor starter in conjunction with a timer.

Momentary push buttons allow for starting or stopping the siren motor starter from any of a number of sites. These buttons can be used alone or together to control the siren, and can be used with devices such as the PGA or program clock.

Program Clocks— 75 and 75WC

The Model 75 Program clock and 75WC clock with day selection and weekend cut-off provide operation of a siren as a time signal or curfew. They provide a 10-second signal automatically at any 5-minute interval during a 24-hour period. Program clocks are equipped with a manual test button and are offered with a synchronous motor for 120- or 240-volt operation.